

## Coil cord with banana plug & female snap

Version 09/15

Item no. 1364527- 1364534

### Coil cord with banana plug & female snap



Item no.	Product description	Model no.	Snap size tolerance ± 0,5mm	Alligator Clip (mm) tolerance ±3mm	Cord length without stretched (cm) tolerance ±5cm	Stretched cord length (cm) tolerance ±5cm
1364527	6 feet Coil cord with banana plug & female snap (snap size 4mm)	SpKL-4-183-SK	4mm	33.8	50	183
1364528	8 feet Coil cord with banana plug & female snap (snap size 4mm)	SpKL-4-244-SK	4mm	33.8	60	244
1364529	10 feet Coil cord with banana plug & female snap (snap size 4mm)	SpKL-4-305-SK	4mm	33.8	70	305
1364530	12 feet Coil cord with banana plug & female snap (snap size 4mm)	SpKL-4-366-SK	4mm	33.8	80	366
1364531	6 feet Coil cord with banana plug & female snap (snap size 10mm)	SpKL-10-183-SK	10mm	33.8	50	183
1364532	8 feet Coil cord with banana plug & female snap (snap size 10mm)	SpKL-10-244-SK	10mm	33.8	60	244
1364533	10 feet Coil cord with banana plug & female snap (snap size 10mm)	SpKL-10-305-SK	10mm	33.8	70	305
1364534	12 feet Coil cord with banana plug & female snap (snap size 10mm)	SpKL-10-366-SK	10mm	33.8	80	366

Color: light blue

Resistance: < 10<sup>6</sup> Ω (Ohms)

Compliance to ESD Norm 61340-5-1