



ARCTIC F Series

High Performance Case Fans

Main Features

- Extremely Quiet
- High air flow and static pressure
- Low noise impeller
- Fluid dynamic bearing extends service life



ARCTIC F Series

Ultra Quiet Case Fans

The **ARCTIC F8, F9 and F12** are exceptionally quiet and cost effective. The patented low noise impeller maximize the air flow, offering high performance at relatively low fan speed.



Specifications:

Voltage:	6-12V
Bearing:	Fluid Dynamic Bearing

ARCTIC F8

Dimensions:	80 L x 80 W x 25 H (mm)
Fan Speed:	2000 RPM
Air Flow:	28 CFM / 47.6 m ³ /h
Noise Level:	0.3 Sone
Weight:	70g

ARCTIC F9

Dimensions:	92 L x 92 W x 25 H (mm)
Fan Speed:	1800 RPM
Air Flow:	35 CFM / 59.5 m ³ /h
Noise Level:	0.4 Sone
Weight:	84g

ARCTIC F12

Dimensions:	120 L x 120 W x 25 H (mm)
Fan Speed:	1350 RPM
Air Flow:	57 CFM / 96.8 m ³ /h
Noise Level:	0.4 Sone
Weight:	108g

Fluid Dynamic Bearing

