

Mechanical characteristics

cables

interface dimensions acc. to assembly code

center conductor
outer conductor

panel piercing
mating life

Components

center contact
outer contact
other metal parts
insulator
crimp ferrule

Electrical characteristics

impedance
frequency
return loss
working voltage
voltage proof
insulation resistance
contact resistance
center contact
outer contact

Environmental

operating temp.
RoHS compliant

Mechanische Eigenschaften

Kabel

Steckgesicht nach Montageanleitung

Innenleiter
Außenleiter
Montagebohrung
Steckzyklen

Bauteile

Innenkontakt
Außenkontakt
sonstige Metallteile
Isolierung
Crimprohr

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Rückflussdämpfung
Betriebsspannung
Prüfspannung
Isolationswiderstand
Durchgangswiderstand
Innenkontakt
Außenkontakt

Umgebung

Betriebstemperatur
RoHS konform

cable group / Kabelgruppe G 4 (RG-179B/U):
0.3LS/1.7S, 1520A Belden, 1521A Belden, 1522A Belden,
179DT Belden Precision Video Cable Analog/Digital
RG-179B/U, RG187A/U

without standard / ohne Norm

A4836
solder / lötl
crimp
Z036
≥ 500

Materials / Material

CuBe2
brass / Messing
brass / Messing
PTFE
brass / Messing

Finish / Oberfläche


Cu1Ni2Au0,3
Cu2Ni5
Cu2Ni5
Cu2Ni5

75 Ω
0-4,5 GHz
TBD
≤ 170 V_{eff} / 50 Hz
500 V_{eff} / 50 Hz
≥ 10 GΩ

≤ 5.0 mΩ
≤ 2.5 mΩ

-55°C / +155°C
2011/65/EU

M 1:1



Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight (g)
			gez./ drawn	07.08.2014	KL	
			gepr./ appr	25.08.2014	VM	ca./approx.
Maßstab/ scale 5:1 (1:1)			Benennung/ title Ultra Tiny BNC Bulkhead Jack HD-BNC-Kabeleinbaubuchse			
untot. Maße/ dim. without tolerances according to			Unterf./ doc. type K	Zeichnungsnr./ drawing no. J01291A0021		
Ersatz für/ replaces						Maße/ dimensions: mm Original : DIN A4 Blatt/ sheet 1 von/ of 1