


M 1:1



Mechanical characteristics

interface dimensions acc. to mating life
coupling torque

Components

centre contact
outer contact
other metal parts
insulator
gasket

Electrical characteristics

impedance
frequency
return loss
insulation resistance
contact resistance
 centre contact
 outer contact

Environmental

operating temp.
protection class
RoHS compliant

Mechanische Eigenschaften

Steckgesicht nach Steckzyklen
Kupplungsdrehmoment

Bauteile

Innenkontakt
Außenkontakt
sonstige Metallteile
Isolierung
Dichtung

Elektrische Eigenschaften

Wellenwiderstand
Frequenz
Rückflussdämpfung
Isolationswiderstand
Durchgangswiderstand
 Innenkontakt
 Außenkontakt

Umgebung

Betriebstemperatur
Schutzklasse
RoHS konform

SMA: IEC 60169-15; R_SMA: ---
>500
79-113 Ncm

Materials / Material



CuZn39Pb3
CuZn39Pb3
CuZn39Pb3
PTFE
MVQ

Finish / Oberfläche

NiP-Au
NiP-Au
ⓐ NiP-Au

50 Ω
0-6 GHz
typ.: 6 GHz-15 dB
≥ 5 GΩ
≤ 3 mΩ
≤ 2 mΩ

-55°C / +155°C
IP 67 (IEC 60529)
2011/65/EU

| | | | | | | |
|------------------|-------------------------------|-------------|---|---|----------------------------|--|
| Änd./ rev. index | Änderungs-Nr. / revision code | Datum/ date | Name/ name | Datum/ date | Name/ name | Gewicht/ weight (g) |
| | | | gez./ drawn | 22.01.2008 | BJ | |
| | | | gepr./ appr. | 12.02.2008 | GE | ca./approx. |
| | | | Maßstab/ scale | Benennung/ title | |  |
| | | | 5:1 (1:1) | Adaptor SMA - RSMA Adapter SMA - R-SMA | | |
| | | | untol. Maße/ dim. without tolerances according to | Untert./ doc. type | Zeichnungsnr./ drawing no. |  Maße/ dimensions: mm |
| | | | | K | J01155R0085 | |
| b | 25356 | 20.11.2013 | KL | | | Original : DIN A4 |
| a | 22486 | 17.01.2011 | MA | Ersatz für/ replaces | | Blatt/ sheet 1 von/ of 1 |