



for connector type (7-16 and N types): SIMFix Pro 7/8", SIMFix CA-Pro 7/8"
SIMFix ST 7/8", SIMFix CA-ST 7/8"

for cable type: G24 (7/8"): RFA 7/8"-50, RFX 7/8"-50, 5228A 7/8"-LD, HPL 50-7/8, HFC22D LS, Flexline 7/8"R, LCF78-50JA, LDF5-50A, AVA5-50, SUCOFEEED 7/8
G52 (7/8" Alu): RFA 7/8"-50 AL, HPL 50-7/8 AL, AL5-50

2009	Datum/ date	Name/ name	Gewicht/ weight (g)	Oberfläche/ surface (mm ²)	Werkstoff/ material
	gez./ drawn	22.06.	PU		
	gepr./ appr.	23.06.09	HR		Oberfläche/ finish
	Norm/ stand.				
Maßstab/ scale	Benennung/ title				
1:1	Manual Stripping Tool 7/8" corrugated cable				
untol. Maße/ dim. without tolerances according to	Untert./doc. type	Zeichnungsnr./ drawing no.			 Maße/ dimensions: mm
	K	N00091A0022			
Änd./ rev. Index	Änderungsmittlung/ revision code	Datum/ date	Name/ name	Ersatz für/ replaces	Original : DIN A4
b	22674	14.03.11	KL		Blatt/ sheet 1 von/ of 1
a	21020	10.07.09	PU		