



Außenleiter / outer conductor	CuZn39Pb3	Cu2Ni5
Innenleiter / inner conductor	CuPb1.15Ni1 (C97)	Cu1Ni2Au0.8
Crimprohr / crimp ferrule	SF Cu w	Ni5
sonstige Metallteile / other metal parts	CuZn39Pb3	Cu2Ni5
Isolierung / insulator	PTFE	
Dichtung / gasket	Silicon	
 Kabel / cable	G 1 : 7806A Belden, 9907 Belden, HPF 195 Harbour Industries, KX 15, LMR-195 TMS, RG-58C/U,	
 Montage / assembly	A3405	

				2004	Datum/date	Name/name	Werkstoff/ material	
				gez./drawn	30.07.	BJ		
				gepr./appr.	30.07.04	HM	Oberfläche/ finish	
				Norm/stand.				
Maßstab/scale	2:1	Benennung/title		R-BNC-Kabelstecker R-BNC Straight Plug			 Telegärtner	
untol. Maße/ dim. without tolerances according to	Untert./doc.type	Zeichnungsnr./drawing no.						
		K	J01000R0000		 Maße/dimensions: mm			
Änd./rev. Index	Änderungsmittellung/ revision code	Datum/ date	Name/ name	Ersatz für/ replaces		Original: DIN A4		