

Mechanical characteristics
interface dimensions acc. to

Mechanische Eigenschaften
Steckgesicht nach

MIL-STD-348A

Components
centre contact
outer contact
other metal parts
insulator
gasket

Bauteile
Innenkontakt
Außenkontakt
sonstige Metallteile
Isolierung
Dichtung

Materials / Material
brass / Messing
brass / Messing
brass / Messing
PTFE
silicone / Silikon

Finish / Oberfläche
gold plated / vergoldet
nickel plated/ vernickelt
nickel plated/ vernickelt

Electrical characteristics
impedance
frequency
voltage rating



Elektrische Eigenschaften
Wellenwiderstand
Frequenz
Betriebsspannung

50 Ω
0-300 MHz
max. 500 V

Environmental
operating temp.
RoHS compliant

Umgebung
Betriebstemperatur
RoHS konform

-55°C / +85°C
2011/65/EU

Änd./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	Datum/ date	Name/ name	Gewicht/ weight (g)
			gez./ drawn	23.04.2013	MA	
			gepr./ appr	24.04.2013	JA	ca./approx.
			Maßstab/ scale	Benennung/ title		
			2:1	Adaptor UHF-N (f-m) Adapter UHF-N (f-m)		
			Unterl./ doc. type	Zeichnungsnr./ drawing no.		 Maße/ dimensions: mm
			K	J01043A0832		
			Ersatz für/ replaces			Original : DIN A4
					Blatt/ sheet 1 von/ of 1	