



Mechanical characteristics

cable group

interface dimensions acc. to assembly code
 panel piercing
 centre conductor
 outer conductor
 mating life

Components

centre contact
 outer contact
 tooth washer
 other metal parts
 insulator
 gasket
 o-ring

Electrical characteristics

impedance
 frequency
 voltage proof
 insulation resistance
 contact resistance
 centre contact
 outer contact

Environmental
 RoHS compliant

Mechanische Eigenschaften

Kabelgruppe

Steckgesicht nach Montageanleitung
 Montagebohrung
 Innenleiter
 Außenleiter
 Steckzyklen

Bauteile

Innenkontakt
 Außenkontakt
 Fächerscheibe
 sonstige Metallteile
 Isolierung
 Dichtung
 O-Ring

Elektrische Eigenschaften

Wellenwiderstand
 Frequenz
 Prüfspannung
 Isolationswiderstand
 Durchgangswiderstand
 Innenkontakt
 Außenkontakt

Umgebung
 RoHS konform

G 1: 7806A, 9907, CNT-195, HPF-195, KX 15, LMR-195, RG-58C/U, WCX195
 G 5: RG223/U, RG-400/U, 1.0/2.95 AF, RG-141A/U, RG-142B/U

IEC 61169-8
 A11
 Z004
 solder/löt
 clamp/klemm
 ≥500

Materials / Material

CuBe2
 CuZn39Pb3
 CuSn6
 CuZn39Pb3
 PTFE
 silicone / Silikon
 NBR

Finish / Oberfläche

Ni2Au0,8
 Cu2Ni5
 Cu2Ni5
 Cu2Ni5

50 Ω
 0-4 GHz
 1,5kV_{eff} / 50 Hz
 ≥ 5 GΩ
 < 20 mΩ
 ≤ 5 mΩ

2002/95/EC

				2011	Datum/ date	Name/ name	Gewicht/ weight (g)	Oberfläche/ surface (mm ²)	Werkstoff/ material	
				gez./ drawn	15.08.	MA				
				gepr./ appr.	15.08.11	BJ			Oberfläche/ finish	
				Norm/ stand.						
			Maßstab/ scale 2:1	Benennung/ title BNC Bulkhead Jack BNC-Kabeleinbaubuchse						
			untol. Maße/ dim. without tolerances according to	Untert./ doc. type K	Zeichnungsnr./ drawing no. J01001A1223					
Änd./ rev. Index	Änderungsmittelung/ revision code	Datum/ date	Name/ name	Ersatz für/ replaces					Original : DIN A4 Blatt/ sheet 1 von/ of 1	

Maße/ dimensions: mm