



EUROLITE Police Light DE-1

Classic police light

- High quality, long-lived technology
- 230 V/ 18 W lamp already installed
- Compact housing

Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power consumption:	24 W
Rotation-speed:	approx. 95 RPM
Dimensions (LxWxH):	200 x 145 x 180 mm
Weight:	0.5 kg

- No. 50603020..... yellow
- No. 50603025..... red
- No. 50603027..... blue
- No. 50603030..... green



EUROLITE LED Police Light PRO 12V High Power

Bright police light

- LED luminaire with 4 x 1 W LED
- Alu housing + alu fixation plate with 4 mounting holes for suction cups
- 2 versions: blue, amber

Technical specifications:

Power supply:	12 V DC
Power consumption:	12 W
LED type:	1 W High Power
Number of LEDs:	4
Dimensions (LxWxH):	ca. 165 x 100 x 60 mm
Weight:	0.4 kg

- No. 50603625..... blue
- No. 50603630..... amber



EUROLITE LED Buzzer Police Light blue

Buzzer light in blue or red

- Rotating double reflector 180° opposed, with an LED as central light source
- For 3x AA 1.5V batteries (not included in delivery)

Technical specifications:

Power supply:	4.5 V DC
Power consumption:	1 W
Fitting battery:	3 x AA 1.5 V (not included in delivery)
Dimensions (LxWxH):	119 x 119 x 106 mm
Weight:	0.20 kg

- No. 50603650..... blue
- No. 50603652..... red



EUROLITE LED Police Light 108 LEDs Classic

LED police beacon classic

- Equipped with 108 LEDs
- Robust PVC housing
- High quality, long-lived technology
- Rotation speeds can be adjusted via the rotary-control

Technical specifications:

Supply voltage (via power unit):	12 V DC
Power consumption:	4 W
Number of LEDs:	108
Rotation speed:	40-240 RPM
Dimensions (LxWxH):	205 x 145 x 180 mm
Weight:	0.75 kg

- No. 51931471..... red
- No. 51931472..... blue