

**DIGITUS<sup>®</sup> Fast Ethernet PoE+ Repeater with 1-port 10/100Mbps in and 2-port 10/100Mbps out**



✓ Extension up to 300 m

✓ PoE powered

✓ 1-Port PoE In / 2- Port PoE

✓ Cost effective solution

**Abstract**

Extend your 100 m Ethernet signal up to 300 meters!

**Features**

Ethernet IEEE802.3 / 802.3u / IEEE802.3 af/at

Ethernet Speed: 10/100Mbps Fast Ethernet

Transmission distance up to 300 m

No additional power supply necessary

PoE - Power over Ethernet

Operating Temperature: -40° C to 75° C

Dimensions (L x W x H): 103 x 82 x 25 mm

Weight: 195 g

## Product Overview

The DIGITUS Fast Ethernet Repeater uses the advanced network cable and power technology to extend your 100 m Ethernet signal up to 300 m. The DN-95122 is self powered by PoE, so there is no additional power supply on the Repeater side needed. This enables you to use the device even where no power lines or outlets are available. You can greatly extend the transmission distance and providing PoE at the same time. It is a perfect, inexpensive and time saving solution for security surveillance and network projects.

## Product Number Information

DN-95122 Fast Ethernet PoE+ Repeater with 1-port 10/100 Mbps in and and 2-port 10/100 Mbps out

## Product Images



## Example of Use

