

DIGITUS Plug&View OptiGuard

DN-16049 4016032362944



DIGITUS Plug&View OptiGuard
2MP H.264 IP 11N Day&Night Outdoor Bullet camera 12V, 2GB TF

Your Plug&View IP camera with outdoor-appropriate IP66-housing and simple installation

This IP camera from the Plug&View Series of DIGITUS® is the new guardian for your garden, garage yard or entrance area. The OptiGuard is thanks to its IP66-housing ideally suited for outdoor use. It is as narrow as inconspicuous and gives you a focused view on lonely corners or potential entrances on your property. The 2-megapixel CMOS sensor with infrared LEDs provides superior video resolution day and night. So you can go sleep in peace. The Plug&View camera is compatible with PC, notebook, and thanks to the free DIGITUS® Plug&View app also with a tablet or smartphone, which enables you to retrieve the surveillance images on the road at any time. The installation is performed easily and quickly for example via QR code scanning. The camera can be operated wirelessly over wireless LAN, the latest 11n standard ensures a liquid transfer.



- 1 2 megapixel video resolution (Full HD 1920 x 1080, HD720 1280 x 720)
- 1 IP66 housing design for outdoor use
- 1 Integrated 2 GB storage for recording videos and snapshots
- 1 Wi-Fi in accordance with the latest 11n standard for seamless transmission
- 1 Video stream with low latency and network load thanks to H.264 compression format
- 1 Simple and quick installation with P2P support and QR code scanning
- 1 Powerful, mobile surveillance with support for iOS and Android devices
- 1 Built-in infrared LEDs and infrared cut-off filters for day and night monitoring
- 1 LAN speed: 10/100Base-TX Ethernet
- 1 Suitable for all common browsers
- 1 Easy mounting with supplied fittings
- 1 Powerful motion detection – automatically records and saves (motion) images via e-mail/FTP server
- 1 Supports up to 25fps video frame rate at HD720 and 15fps at Full HD
- 1 Operating temperature: -20 to +60 °C
- 1 Power source (±10 %): DC12 V / 1 A
- 1 Supports the DIGITUS® Plug&View app for smartphones and tablets
- 1 Lens: F1.5 / 3.6 mm
- 1 Horizontal viewing angle: 69°
- 1 WPS (Wireless Protected Setup) feature provides easy, quick, and secure encryption for your wireless connection
- 1 Minimum Internet requirements: DSL 1000 (1,024 kbps download/384 kbps upload)
- 1 Minimum requirements for smartphone access: 3G network connection
- 1 Dimensions (mm): 180 (L) x 60 (W) x 65 (H)

Package Content

- 1 IP camera
- 1 Product support CD-ROM
- 1 Mounting kit
- 1 Power Supply
- 1 with 2 GB internal storage

DIGITUS Plug&View OptiGuard

DN-16049 4016032362944



→ Logistics

| | Number (pcs) | Weight (kg) | Depth (cm) | Width (cm) | Height (cm) | cm³ |
|------------------------------|--------------|-------------|------------|------------|-------------|----------|
| Packaging Unit Carton | 18 | 13,80 | 41,50 | 41,50 | 33,00 | 56834,25 |
| Packaging Unit Inside | 1 | 0,77 | 10,00 | 20,00 | 12,50 | 2500,00 |
| Packaging Unit Single | 1 | 0,77 | 10,00 | 20,00 | 12,50 | 2500,00 |
| Net single without Packaging | 1 | 0,00 | 14,00 | 7,50 | 8,00 | 840,00 |

→ Operating systems



→ Packaging type

