



MATERIAL LIST:

⑤	HOOD MOLDED	BEIGE PVC	2	
④	SCREW	#4-40 THUMB SCREW, NICKEL PLATED	4	
③	CONNECTOR	DB 9PIN FEMALE: SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL	1	
②	CONNECTOR	DB 9PIN MALE: SOLDER TYPE, BLUE INSULATION, GOLD FLASH CONTACTS, NICKEL PLATED SHELL	1	
①	CABLE	30AWG (7/0.10CCS)*9C+7/0.12CCS+AM+PVC/BEIGE OD: 5.4 ± 0.2MM	1	

NOTE:

1. 100% open short & miss wire test;
2. RoHS2.0 AND REACH COMPLIANT
3. MARKING: COMPUTER INTERFACE CABLE 300V 80°C

PARTS NAME		SPECIFICATION DESCRIPTION			QT'Y	REMARK	CUSTOMER			ITEM NO.	29212C33		
							PRODUCT NAME	DB9 MALE TO FEMALE CABLE		UNO ITEM NO.		UNIT	MM
		NEW			2015.07.08	A	DRAWNBY	CHECKBY		APPOBY	DATE		
BY	CHK	REVISION RECORD MODIFICATIONS			DATE	REV.	FERGUS	ALVAN		2015.07.08			