



Peach Star Binder Pro - PB200-30

Product Bulletin

Peach Art. 00510913

Binding Method	Spiralbindung / Plastic Comb Binding
Manual Punch / Manual Binding	Ja / Yes
Max. Working Width [mm]	303
Binding Capacity [sheets [80 g/m2]]	350
Peach Nr	PB200-30
Max. Diameter of Plastic Binding Combs [mm]	38
Punch Capacity [sheets [80 g/m2]]	12
Punch Capacity [laminated sheet]	1
Punched Holes per A4 size sheet	4 / 21
4-hole Punch	Ja / Yes
Product net weight [kg]	2.400
Product gross weight [kg]	2.800
Master Carton Weight [kg]	18.0
Product Dimensions (l x w x h) [cm]	42.0 x 18.5 x 29.5
Box Dimensions (l x w x h) [cm]	42.0 x 29.0 x 18.0
Master Carton Dimensions (l x w x h) [cm]	63.0 x 44.0 x 40.0
Units per master carton	4
Units per Pallet (120 x 80 x 170) [cm]	48
Units per Container 20"	1'040
Units per Container 40"	2'160
Units per Container 40" HC	2'540
EAN code	7640162832373
Customs tariff number	8440.1030
Made in	China

Features

- Die weltweit meistverkaufte Bindemaschine, NEU nun noch einfacheres Handling -
- Keine Fehllochung mehr dank neuer Papierführung - Für Binderücken von 6 bis 38 mm -
- Zusätzlicher 4-fach Locher integriert

13.04.15