100V

OMNITRONIC OD-2 Wall speaker 2x

Universal wall speaker pair

- 100 V PA speaker system for general applications
- 1-way system with 30 W power and 100 V transformer
- 6 cm full-range speaker (2.5")
- · Attractive ABS plastic cabinet (scratch-resistant) with metal grille
- Durable mounting plate with joint for panning and tilting allows ceiling or wall installation in most varying angles







Technical specifications:

| Input voltage: | 100 V |
|-------------------------|-------------------------------|
| Rated power: | 15 W RMS |
| Program power: | 30 W |
| Speaker: | 6 cm (2.5") |
| Connections: | spring clamps |
| Sensitivity: | 88 dB (1 W, 1 m) |
| Max. SPL: | 92 dB (1 m) |
| Frequency range: | 150 Hz - 22 kHz |
| Dispersion angle (HxV): | 60° x 60° |
| Dimensions (H x W x D): | 111 x 87 x 90 mm |
| Weight (piece): | 0.5 kg (incl. mounting plate) |
| | |

| No. 11036902 | OD-2T, | blacl |
|--------------|--------|-------|
| No. 11036903 | 0D-2T, | white |







OMNITRONIC OD-22 Wall speaker

Universal wall speaker system

- 100 V PA speaker system for general applications
- 2 x 6 cm full-range speaker (2 x 2.5")
- 3.5 x 6 cm passive membrane
- 100 V transformer
- Durable mounting plate with joint for panning and tilting allows ceiling or wall installation in most varying angles





Technical specifications:

| Input voltage: | 100 V | |
|-------------------------|------------------------------------|--|
| Rated power: | 15 W RMS | |
| Program power: | 30 W | |
| Speaker: | 2 x 6 cm (2 x 2.5") | |
| Connections: | spring clamps with parallel output | |
| Sensitivity: | 88 dB (1 W, 1 m) | |
| Max. SPL: | 92 dB (1 m) | |
| Frequency range: | 120 Hz - 22 kHz | |
| Dispersion angle (HxV): | 60° x 60° | |
| Dimensions (H x W x D): | 110 x 209 x 109 mm | |
| Weight: | 0.9 kg (incl. mounting plate) | |
| | | |

| No. 11036908 | ODT-22, | blac |
|--------------|---------|------|
| No. 11036909 | ODT-22, | whit |