



IP65 ACTIVE

OMNITRONIC OD-4 Wall speaker 2x

Weatherproof wall speaker pair

- Passive (8 ohms) and active PA speaker systems with an excellent sound for general applications
- 2-way system with 10/13.5/16.5 cm cm woofer (4/5.25/6.5") and 1.5/2.5 cm tweeter (0.5/1")
- Weatherproof (IP65) plastic cabinet with metal grille and cover for the connectors (passive models)
- Panning and tilting mounting bracket allows ceiling or wall installation in most varying angles

No. 11036912	OD-4, black, 8ohms
No. 11036913	OD-4, white, 8ohms
No. 11036918	OD-5, black, 8ohms
No. 11036919	OD-5, white, 8ohms
No. 11036922	OD-5A, black, active
No. 11036923	OD-5A, white, active
No. 11036924	OD-6, black, 8ohms
No. 11036925	OD-6, white, 8ohms
No. 11036928	OD-6A, black, active
No. 11036929	OD-6A, white, active



Technical specifications:

Device:	OD-4, 8 ohms	OD-5, 8 ohms	OD-5A, active	OD-6, 8 ohms	OD-6A, active
Power supply:			230 V AC, 50 Hz		230 V AC, 50 Hz
Rated power:	30 W RMS	35 W RMS	35 W RMS	40 W RMS	45 W RMS
Program power:	60 W	70 W	70 W	80 W	90 W
Input:					
Circuitry:			class D		class A/B
Components:	10 cm woofer (4"), 1.5 cm tweeter (0.5")	13.5 cm woofer (5.25"), 1.5 cm tweeter (0.5")	13.5 cm woofer (5.25"), 1.5 cm tweeter (0.5")	16.5 cm woofer (6.5"), 2.5 cm tweeter (1")	16.5 cm woofer (6.5"), 2.5 cm tweeter (1")
Connections:	screw terminals	screw terminals	RCA, unbal., spring terminals, bal.	screw terminals	RCA, unbal., 3.5 mm stereo jack, unbal., spring terminals, bal.
Rated power:					
Sensitivity:	88 dB (1 W, 1 m)	89 dB (1 W, 1 m)	89 dB (1 W, 1 m)	90 dB (1 W, 1 m)	89 dB (1 W, 1 m)
Max. SPL:	91 dB (1 m)	92 dB (1 m)	93 dB (1 m)	93 dB (1 m)	96 dB (1 m)
Impedance:	8 ohms	8 ohms		8 ohms	
Frequency range:	100 Hz - 20 kHz	80 Hz - 20 kHz	80 Hz - 20 kHz	50 Hz - 20 kHz	80 Hz - 20 kHz
Dispersion angle (HxV):	170° x 170°	170° x 170°	170° x 170°	170° x 170°	170° x 170°
Dimensions (L x W x H):	125 x 125 x 195 mm	163 x 160 x 255 mm	163 x 160 x 255 mm	190 x 195 x 290 mm	195 x 195 x 300 mm
Weight (piece):	1.3 kg (incl. bracket)	2.2 kg (incl. bracket)	3 kg (incl. bracket)	3 kg (incl. bracket)	4.4 kg (incl. bracket)