



EUROLITE RF-1200 Radial blower

Wind machine

- 3 speed modes
- 3 discharge angles
- Qualified for road use

No. 80208051

Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power consumption:	1200 W
Speed:	1200 -1300 RPM
Maximum airflow:	60 m ³ /min
Dimensions (LxWxH):	500 x 455 x 480 mm
Weight:	17 kg



DMX

ANTARI AF-5R Effect Fan

Wind machine with DMX interface

- 3 speed modes
- DMX interface
- Qualified for road use
- Wireless transmitter available as accessory

No. 80208053

Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power:	1.2 kW
DMX512 connection:	5-pin XLR
Dimensions (LxWxH):	530 x 470 x 490 mm
Weight:	18 kg



EUROPALMS Rotary plate 25cm up to 25kg

Base with rotary plate

- Base with rotary plate for decoration, lighting effects and much more
- Applicable for 25 kg maximum load

No. 50701195

Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power consumption:	4.5 W
Rotation speed:	approx. 1 RPM
Maximum load:	25 kg
Dimensions (LxWxH):	255 x 255 x 59 mm
Weight:	1.2 kg



EUROPALMS Rotary plate 45cm up to 50kg

Base with rotary plate

- 5 rotations per minute
- Applicable for 50 kg maximum load

No. 50701200

Technical specifications:

Power supply:	230 V AC, 50 Hz ~
Power consumption:	3 W
Rotation speed:	approx. 0.5 RPM
Maximum load:	50 kg
Dimensions (LxWxH):	450 x 450 x 58 mm
Weight:	4 kg