

DMX



### EUROLITE DPX-610 DMX dimmer pack

Digital 6-channel dimmer pack

- Channel outputs via pole connectors
- 6 channels x 10 A

No. 70064120

#### Technical specifications:

Power supply:	230-380 V AC, 50 Hz ~
Max. power output:	13800 W
Max. current:	60 A
Number of control channels:	6
Max. output/channel:	2300 W
Max. current/channel:	10 A
Integrated programs:	12
Output sockets:	via pole connectors
Circuit breaker:	6 x C 10 A
Dimensions (WxDxH):	410 x 482 x 95 mm
	Rack installation with 2 U
Minimum mounting depth:	500 mm
Weight:	8 kg


DMX



### EUROLITE DPX-610 S DMX dimmer pack

Digital 6-channel dimmer pack

- Channel outputs via safety sockets
- 6 channels x 10 A



No. 70064122

#### Technical specifications:

Power supply:	230-380 V AC, 50 Hz ~
Max. power output:	13800 W
Max. current:	60 A
Number of control channels:	6
Max. output/channel:	2300 W
Max. current/channel:	10 A
Integrated programs:	12
Output sockets:	Safety sockets
Circuit breaker:	6 x C 10 A
Dimensions (WxDxH):	410 x 482 x 95 mm
	Rack installation with 2 U
Minimum mounting depth:	500 mm
Weight:	8 kg

DMX



### EUROLITE DPX-610 MP DMX dimmer pack

Digital 6-channel dimmer pack

- Outputs via two industrial sockets
- 6 channels x 10 A



No. 70064125

#### Technical specifications:

Power supply:	230-380 V AC, 50 Hz ~
Max. power output:	13800 W
Max. current:	60 A
Number of control channels:	6
Max. output/channel:	2300 W
Max. current/channel:	10 A
Integrated programs:	12
Output sockets:	two 16-pin sockets
Circuit breaker:	6 x C 10 A
Dimensions (WxDxH):	443 x 482 x 95 mm
	Rack installation with 2 U
Minimum mounting depth:	500 mm
Weight:	8.5 kg

DMX



### EUROLITE DPX-620 DMX dimmer pack

Digital 6-channel dimmer pack

- Channel outputs via pole connectors
- 6 channels x 20 A

No. 70064130

#### Technical specifications:

Power supply:	230-380 V AC, 50 Hz ~
Max. power output:	27600 W
Max. current:	120 A
Number of control channels:	6
Max. output/channel:	4600 W
Max. current/channel:	20 A
Integrated programs:	12
Output sockets:	via pole connectors
Circuit breaker:	6 x C 20 A
Dimensions (WxDxH):	420 x 482 x 95 mm
	Rack installation with 2 U
Minimum mounting depth:	500 mm
Weight:	8 kg