

VARIABLE SPEED

75 mm

120 W

PERFECT GRINDING / POLISHING RESULTS

VARIABLE SPEED
0 – 9900 RPM



HG34 | 3" GRINDER-POLISHER WITH ACCESSORY SET

THIS COMPACT, YET POWERFUL VARIABLE SPEED BENCH GRINDER & POLISHER IS IDEAL FOR DIY AND SMALL WORKSHOP USE. INCLUDED WITH THE GRINDER IS A FLEXI DRIVE COMPLETE WITH A 100 PIECE TOOL KIT SUITABLE FOR CONVERTING THIS BENCH TOP TOOL INTO A UNIQUE MULTI-PURPOSE GRINDER, POLISHER AND SANDING TOOL.

- Variable speed 0 – 9900 rpm
- Includes 100 pcs grinding kit containing flexible drive accessories for grinding, polishing and sanding
- Flexible drive kit for additional cutting, grinding & polishing away from the unit
- Eye shields protect you from flying debris without obstructing your view
- Grinding / polishing wheel diameter Ø 75 mm



LOGISTICAL DATA

20 Container	2050 pcs
40 Container	4200 pcs
40 HQ Container	4700 pcs

SPECIFICATIONS

Dimensions L x W x H	230 x 130 x 145 mm
Disc size	75 mm
Speed	0 – 9900 rpm
Weight	3.1 kg
Motor	230 V
Input	120 W
Order No	5903106901
Barcode	4046664036555