




<i>Item</i>	<i>Length</i>
-----	$110 \pm 10\text{mm}$

REVISION			
REV	DESCRIPTION	DATE	SIGNATURE
A	Initial release	2015.08.04	GINO



Cable construction

Wiring Method

⑥	-----	2.5 4 Pole (Female) Plug	1	brass	Good-plated
⑤	335-014-1	Shell	1	AL	Black
④	sS00-078	Inner molding	1	PVC	Black (107-5652-87)
③	335-012-1	Shell	1	AL	Black
②	S00-048	Inner molding	1	PVC	Black (107-5652-87)
①	335-015	3.5 4 Pole (M) Plug	1	brass	Good-plated
No	PART No.	COMPONENTS	QTY	MATERIAL	FINISH

TITLE			DRAWING No.		
3.5 4 pole (M)-2.5 4 pole (F)			SHEET 1/1		
UNIT	SCALE	TOL UNLESS NOTED	APPROVED BY	CHECKED BY	DRAWN BY
mm	free	± 0.1			GINO
					2015.08.04