




Power cable feed-through	Primary rated current	Secondary rated current	Rated power	Accuracy class	Cable length	Item No.	Pack. Unit
Ø 18 mm	60 A	1 A	0.2VA	3	3 m	855-3001/060-003	1
	100 A	1 A	0.2VA	3	3 m	855-3001/100-003	1
	200 A	1 A	0.2VA	1	3 m	855-3001/200-001	1
	250 A	1 A	0.2VA	1	3 m	855-3001/250-001	1




Power cable feed-through	Primary rated current	Secondary rated current	Rated power	Accuracy class	Cable length	Item No.	Pack. Unit
Ø 18 mm	100 A	1 A	0.2VA	1	3 m	855-4001/100-001	1
	150 A	1 A	0.2VA	1	3 m	855-4001/150-001	1
	150 A	5 A	1VA	1	0.5 m	855-4005/150-101	1
	200 A	1 A	0.2VA	0.5	3 m	855-4001/200-001	1



Power cable feed-through	Primary rated current	Secondary rated current	Rated power	Accuracy class	Cable length	Item No.	Pack. Unit
Ø 28 mm	200 A	1 A	0.2VA	1	3 m	855-4101/200-001	1
	250 A	1 A	0.2VA	1	3 m	855-4101/250-001	1
	250 A	5 A	1VA	1	0.5 m	855-4105/250-101	1
	400 A	1 A	0.2VA	1	3 m	855-4101/400-001	1
	400 A	5 A	1VA	1	0.5 m	855-4105/400-101	1



Power cable feed-through	Primary rated current	Secondary rated current	Rated power	Accuracy class	Cable length	Item No.	Pack. Unit
Ø 42 mm	400 A	1 A	0.5VA	0.5	5 m	855-5001/400-000	1
	400 A	5 A	0.5VA	1	3 m	855-5005/400-001	1
	600 A	1 A	0.5VA	0.5	5 m	855-5001/600-000	1
	600 A	5 A	0.5VA	0.5	3 m	855-5005/600-000	1
	1000 A	1 A	0.5VA	0.5	5 m	855-5001/1000-000	1
	1000 A	5 A	0.5VA	0.5	3 m	855-5005/1000-000	1



Power cable feed-through	Primary rated current	Secondary rated current	Rated power	Accuracy class	Cable length	Item No.	Pack. Unit
Ø Ø 42 mm x 48	1000 A	1 A	0.5VA	0.5	5 m	855-5101/1000-000	1
	1000 A	5 A	0.5VA	0.5	3 m	855-5105/1000-000	1