

# Stub Antenna with RPSMA Plug



The antenna is equipped with a knee lever, which can be swiveled to 90 degrees. It has a 1/2-wave coaxial dipole and the coupling allows 360° rotation.

## FEATURES AND BENEFITS

- External antenna for CANblue II
- RP-SMA Connector (female)
- Length 10 cm (including connector)
- Frequency 2.4 GHz
- FCC Part 15 compliant polarized connector

<b>ORDER NUMBER</b>	<b>1.04.0085.00001</b>
CAN connector	RP-SMA (female)
Current rating	50 watts
Temperature range	-40 °C to +80 °C
Length	100 mm