



DATASHEET

CCA Power Cable , 1.50 mm² , OD:3.2 mm

Version 06/15

- Item no. 1386600 (Red)
- 1386601 (Black)
- 1386602 (Blue)

Jacket, outer dimension.....	PVC 3.2 mm
Length.....	5 meter
No. of conductors.....	59 x 0.18 mm
Strand per conductor.....	1.5 mm ²
Conductor material	CCA
Insulation material	PVC
Dielectric strength	26 MV/m
Rated voltage.....	< AC 50V / DC 75V
Max. load capacity.....	4A
Conductor resistance.....	27ohm/km
Insulator resistance.....	Min 200M ohm x km
Operating temperature.....	-20 to +70 C
Storage temperature range.....	-20 to +70 C
Operating humidity range.....	35%~95%
Storage humidity range.....	35%~95%



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.