



Technical Data:

Electrical:

- Voltage rating: 12VDC
- Current rating: 5A
- Contact resistance: <20mΩ
- Insulation resistance: 500MΩ / DC500V
- Wire range: 24-18AWG

Mechanical:

- Torque: 0.2Nm (1.8lb/in)
- Operating temperature: -40°C to 105°C
- Strip length: 4.5-5mm

DATE	REVISION	APPROVAL BY	DIMENSION	mm ±0.3	MODEL No	LT-PJ-2.5-4C
			DRAW BY	Camily Pun	NAME	4 Conductor 2.5mm Female Jack Adaptor
			APPROVAL BY	Rikki So		
			DATE	01-05-2015		