



Models	Palfinger Scanreco 590 960

Compatibility

Battery Model: Palfinger Scanreco 590 592 960 Funkfernsteuerung

Physical Characteristics

Dimension: 132.1 X 113.8 X 67.8 mm (5.2 X 4.48 X 2.67 inch)

Weight: No PSU: 230 g (7.40 oz.); With PSU: 800 g (25.72 oz.)

Plastic Material: ABS + PC

Electrical Characteristics

Charge Chemistry: Ni-Cd, Ni-MH

Input Voltage: 10.0V ~ 24.0V

Maximum Charge Current: 1200mA

Power Supply: External with safety approval

AC Input: 110V, 230V, 240V

Charge Mode: Ni-Cd / Ni-MH: Constant current

Discharge Current: 0.22A ~ 0.38A

LED Display

No LED Display: Standby Mode

Steady Red LED: Charging

Steady Green LED: Charge Completed

Flashing Green LED: Discharging

Flashing Red LED: Fault

User Environment

Operation Temperature: 0 ~ +40°C (+32 ~ +104°F)

Agency Approval: CE for the charging unit