



Dip Type Tact Switch

Version 02/16

Item no. 1386947



1. Rating : DC12V 50mA
2. Travel : 0.25 ± 0.1 mm
3. Operating Force : 100, 130, 160, 250 ± 50 gf
4. Contact Resistance : $100\text{m}\Omega$ Max
5. Life : 100,000 Cycles Min

Knob Height mm

Code	Blank	A	B	C	D	E	F	G	H	I	J	K	L	M
Standard(L)	4.3	5	6	6.3	7	7.3	8	8.5	9.5	12.5	13.0	13.5	17	45
Bracket Type(L)	3.15	3.85	4.85	5.15	5.85	6.15	6.85	7.35	8.35	11.35	11.85	12.35	15.85	3.35

Distributed by Conrad Electronic SE

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.