

483 mm (19") Wall Mounting Cabinets Dynamic Basic Series



✓ 0.8 - 1.2 mm strong sheet steel

✓ Safety class IP20

✓ Loading capacity: 60 kg

✓ Large range of equipment available

Abstract

483 mm (19") Wall Mounting Cabinets - Dynamic Basic Series, 600 mm width - 450 mm, 600 mm depth

Features

- Safety class rating IP20
- Lockable safety-glass door with steel frame
- 210° door opening angle
- 1-point-locking-mechanism on the front door
- 483 mm (19") profile rails mounted on the front side inside of the cabinet, galvanized
- 600 mm depth cabinets with 483 mm (19") profile rails on the front- and rear side
- 483 mm (19") profile rails are adjustable in depth and with height unit marking
- Load capacity of 483 mm (19") profile rails: 60 kg
- Max. 483 mm (19") equipment mounting depth: 365 mm (450 mm depth cabinet); 500 mm (600 mm depth cabinet)
- 0.8 - 1.2 mm strong sheet steel with high load capacity, powder coated
- Cable entry on the rear side, roof and base (pre-punched break-outs)
- Sizes of rear break-outs (HxW in mm): 100x350 mm (7U); 240x350 mm (9U); 380x350 mm (12U & 16U)
- Roof is prepared for fan units (punched out entries)
- Ventilation slots for active and passive ventilation and exhausting
- 3 earthing points (base, side panel and front door)

Product Overview

The Wall Mounting Cabinets of the Dynamic Basic Series are made of a robust steel construction. Stability is given due to the welding spots. The side sections are detachable and the installation on the wall is easy so it can be implemented quickly. Due to their flexibility the cabinets are ideal for all current IT and telecommunication applications.

Logistic Data

Height units (U)	Height in mm	Product dimensions (HxWxD) in mm	Packaging dimensions (HxWxD) in mm	Net-/Gross weight in kg
7U	416.15 mm	600x450 mm	500x680x530 mm	13.8 kg / 15.7 kg
		600x600 mm	500x680x680 mm	17.7 kg / 20.1 kg
9U	505.05 mm	600x450 mm	590x680x530 mm	15.5 kg / 17.5 kg
		600x600 mm	590x680x680 mm	19.9 kg / 22.5 kg
12U	638.40 mm	600x450 mm	720x680 x530 mm	18.3 kg / 20.5 kg
		600x600 mm	720x680x680 mm	23.5 kg / 26.3 kg
16U	816.20 mm	600x450 mm	900x680x530 mm	22.1 kg / 24.8 kg
		600x600 mm	900x680x680 mm	28.4 kg / 31.8 kg

Product Number Information

Item code	Width x Depth in mm	Height units (U)	Color
DN-19 07-U-EC	600x450 mm	7	Grey (RAL 7035)
DN-19 09-U-EC		9	
DN-19 12-U-EC		12	
DN-19 16-U-EC		16	
DN-19 07U-6/6-EC	600x600 mm	7	Grey (RAL 7035)
DN-19 09U-6/6-EC		9	
DN-19 12U-6/6-EC		12	
DN-19 16U-6/6-EC		16	

Product Images



Technical Drawings

