

The information provided herein is from CONNELY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNELY or its affiliates. Unauthorized use of this information for any purpose without the prior written permission of CONNELY is strictly prohibited. CONNELY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

Dept	Qty
DC	1
ED	1
IE	1
ISO	1
PD	1
R&D	1
SD	1
QA	1
QC	1
QE	1

C


D

E


F

G

H



(Series Image-Reference Only)



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 11/05/08'		LJC 11/05/08'
B	ADD PACKING TYPE	YCH 11/18/13'		LJC 11/18/13'
C	DRAWING UPDATE	JLZ 01/18/18'	HZW 01/18/18'	LJC 01/18/18'
D	DRAWING UPDATE	JLZ 02/13/19'		

Notes:

Specifications:

1. Contact Resistance: 20mΩ Max.
2. Insulation Resistance: 1000MΩ Min.
3. Dielectric Withstanding Voltage: 300V AC(rms) For 1 Minute.
4. Current Rating:1A.
5. Temperature: -40°C~+105°C.

Materials:

1. Contact Material: Copper Alloy.
2. Contact Plating: Gold Plating Over Nickel.
3. Insulator Materials: PA-9T,Black,UL94-V0.

Product Number Code:

DS1065-05 - X X X X X X X X

- Post support
S:W/ Post
N/A Code:W/O Post
- Packing type
R:Tape on reel
B:Tube
T:Tray(For N≤3)
- Pick up support
S:W/ Pick up
X:W/O Pick up
- Mounting type
S:SMT type
- Housing color
B:Black
- Contact plating
8: Full gold flash
- Connector type
S:Socket
- No.of contacts
2x2-2x40

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	FEMALE HEADER PITCH 1.27mm	
X.	±0.60	X.	±5°	UNITS	mm		S.M.T TYPE	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1065-05 SERIES	
.XX	±0.25	.XX	±2°	晨翔电子有限公司 CONNFLY CONNFLY ELECTRONIC CO. LTD				
DRAWING TYPE		CUSTOMER						
SCALE		1:1	SHEET 1 OF 1					
DRAWING NO.		C-DS1065-05-XXXXX-D						



晨翔电子有限公司
CONNFLY CONNELY ELECTRONIC CO., LTD