



Dept
Qty
DC 1
ED 1
IE 1
ISO 1
PD 1
R&D 1
SD 1
QA 1
QC 1
QE 1

The information provided herein is from CONNLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNLY or its affiliates. Unauthorized use of this information for any purpose without the prior written permission of CONNLY is strictly prohibited. CONNLY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LL 09/11/06'		LJC 09/11/06'
B	Arrangement drawing	JLZ 12/23/15'	HZW 12/23/15'	LJC 12/23/15'
C	DRAWING UPDATE	JLZ 08/27/18'		

NOTES:

1. Material

- 1.1 Insulator: Thermoplastic(UL 94V-0).
1.2 Contact: Copper alloy.



2. Specification

- 2.1 Temperature range:-40°C~+105°C.
2.2 Contact resistance:20mΩ max.
2.3 Insulation resistance:1000MΩ min.
2.4 Dielectric withstanding voltage:AC 500V per minute.

3. Product number code:

DS1015 - X X X X X

- Housing color
A:Gray
B:Black
Contact plating
2: Gold flash + Nickel
Strain relief
N:W/O
Screw hole
M:W/ Screw hole
N:W/O Screw hole
No. of contacts
10 14 16 20 24 26
30 34 40 50 60 64



(Series Image-Reference Only)

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	IDC BOX HEADER MATES WITH PITCH 1.27mm FLAT CABLE
X.	±0.60	X.	±5°	UNITS	mm		
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	
.XX	±0.25	.XX	±2°			DS1015 SERIES	
DRAWING TYPE		CUSTOMER			 晨翔电子有限公司 CONNFLY ELECTRONIC CO. LTD		
SCALE		1:1	SHEET	1 OF 1			
DRAWING NO.		C-DS1015-XXXXX-C					

INDICATOR SYMBOLS		INDICATOR SYMBOLS	
INDICATOR SYMBOLS		INDICATOR SYMBOLS	
INDICATOR SYMBOLS		INDICATOR SYMBOLS	