


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
UPDATE DRAWING	7
R.STA.MONICA	JUN.27/2012



NOTE:

1. CAVITY CONFORMS TO FCC RULES REGULATIONS PART 68, SUBPART F.

2. MATERIALS:


HOUSING: PBT POLYESTER UL 94V-0
MIXED GLASS FIBER
STANDARD COLOR: BLACK
SHIELD: 0.25MM THICK COPPER ALLOY,
NICKEL PLATED
CONTACTS: 0.35MM THICK PHOSPHOR
BRONZE, WITH SELECTIVE
GOLD PLATING ON CONTACT
AREA AND GOLD FLASH
PLATING AT SOLDER AREA

PART NO.	GOLD PLATING
A00-108-222-450	GOLD FLASH
A00-108-322-450	15 MICROINCHES OF GOLD
A00-108-622-450	30 MICROINCHES OF GOLD
A00-108-922-450	50 MICROINCHES OF GOLD



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES AND 2011/65/EU FOR RoHS COMPLIANCY.

SHIELDED RJ45 TOP ENTRY P.C.B MODULAR JACK		ACAD REF. DWG.: A00-108-222-450	
		DRAWN: F.JAWDI	DATE: FEB. 11/03
EDAC INC TORONTO, ONTARIO CANADA YOUR CONNECTION TO QUALITY & SERVICE		CHECKED:	DATE:
		SCALE: 1:1	SHEET 1 OF 1
TOLERANCE UNLESS NOTED .00 mm ± 0.15 .000 Inch ± .006		DRAWING NUMBER A00-108-222-450	
ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		ISSUE 7	



THIS SERIES FULLY CONFORMS TO THE EUROPEAN UNION DIRECTIVES AND 2011/65/EU FOR RoHS COMPLIANCY.

PACKAGING
TOP ENTRY P.C.B MODULAR JACK

EDAC EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

TOLERANCE UNLESS NOTED
.00 mm ± 0.15
.000 Inch ± .006

ARE THE PROPERTY OF EDAC INC. AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

ACAD REF. DWG.: A00-108-222-450	
DRAWN: R.STA.MONICA	DATE: APR.22/14
CHECKED:	DATE:
SCALE: 1:1	SHEET 1 OF 1
DRAWING NUMBER A00-108-222-450	ISSUE 1