



RoHS Compliant

P1



WIRE ADDRESS

	P2	P1	P3
1+2+3	ORANGE	1+2+3	ORANGE
4+5+6	BLACK	4+5+6	BLACK
7+8+9	RED	7+8+9	RED
10+11+12	BLACK	10+11+12	BLACK
13+14+15	YELLOW	13+14+15	YELLOW



Electrical Test:
 1.100% TEST OPEN SHORT MIS-WIRE
 2.CONTACT RESISTANCE:3Ω MAX.
 3.INSULATION RESISTANCE:5MΩ MIN.
 4.HI-PORT:300V DC/10MS

H	更新彩盒版本为V4	2020-11-12
G	新增線上CE貼紙	2019-10-24
F	去除透明圓貼	2019-04-26
E	更改SATA 15P公頭模型	2016-01-15
VER	REVISE	DATE

NUMBER	BOM.NO	PRODUCT SPECIFICATIONS	Quantity	Unit
D	1 Z-1396406	45P BLACK PVC	1	PCS
C		SATA15P MALE(MALE Welding 180°)		
B		SATA15P FEMALE(BLACK INSULATOR)		
A		UL1007,18# WIRE(YELLOW*2PCS,BLACK*4PCS,RED*2,ORANGE*2)PVC JACKET.		

Company: CONRAD	
Item	1396406
Draw	Kobe Date: 2015.10.14
Approval	
Duty	F16 BOM.NO:12077


RoHS Compliant

CONRAD
GERMANY
BEST NO.: 1396406
PCS.: 100 PCS
MODEL NO.: S15S1560105
ORDER NO.:
WEIGHT(KG.): KGS



外箱側麥

CONRAD
HAMBURG
C/NO.:
MADE IN CHINA



外箱正麥



產品直接裝入VP1-20款彩盒內(105*140*20mm)



100PCS/CTN (580*230*230mm) 一排50pcs 上下兩排



D	更改彩盒為第V3版	2015-12-24
C	去掉PE袋包裝	2015-12-11
B	更改彩盒為第二版	2015-10-27
VER.A	REVISE	DATE

Company: CONRAD

Item	1396406	
Draw	Kobe	ate: 2015.10.14
Approval		
Duty	F16	BOM.NO:12077