

# WFT-3

## Internet Radio / DAB+ / FM-RDS / USB Network Music Player Digital Receiver

Color



Black



Features	<b>Specifications</b>	Photo gallery	
Description			

<b>TUNER</b>	DAB	Band III Frequency (MHz)	174 - 240 (W / DAB+)	
	FM	Frequency (MHz)	87.5 - 108	
		RDS	PS / PTY / CT / RT	
	WiFi	IEEE 802.11 b / g (GHz)	2.4 GHz / 5 GHz	
		Internet Radio (iRadio)	vTuner	
Media Player (mPlayer)		UPnP		
<b>TUNING</b>		Memory Presets	15 (5 iRadio, 5 DAB+, 5 FM)	
<b>MEDIA</b>	USB playback		V	
<b>AUDIO DECODE</b>		Internet Radio (iRadio)	MP3 / WMA / Real Audio	
		Media Player (mPlayer)	MP3 / WMA	
		CD / SD / USB	USB Playback	
<b>CLOCK</b>	Real time	Time	iRadio / DAB / FM RDS-CT	
	Alarm	Radio / iRadio / Buzzer / Media	Radio / iRadio / Buzzer	
		Adjustable Alarm Level	V	
	Snooze		V	
	Sleep		V	
<b>DISPLAY</b>		LCD / VFD / Dial Scale	3.2" TFT LCD	
		View Area (mm / inch)	48.3 x 12.7 / 1.9 x 0.5	
		Graphic / Character Type	Graphic 320 x 240	
		Back Light	V	
<b>FEATURE</b>		Stereo	Earphones	
		Spotify	V	
		Rechargeable	V	
		Software Upgrade	Via Internet	
<b>AUDIO</b>	Sound effect	Treble / Bass Control	V	
		EQ (Sound Effect Selection)	7 (Flat / Jazz / Rock / Movie / Classic / Pop / News)	
<b>OUTPUT POWER</b>		Earphones	1 + 1 mW	
<b>I/O SOCKET</b>		Power	AC - in	
		Aux - in	V	
		Line - out	V	
		Earphones	V	
		USB	Charge (DC Out 5 V / 1 A in standby mode) / Playback	
		Ext. Antenna	V	
		RJ - 45 (Ethernet)	V	
	<b>POWER SUPPLY</b>		Power supply	AC
	<b>ACCESSORIES</b>		Remote Control	V (remote control + app)
<b>DIMENSIONS</b>		Width (mm/inch)	430 / 16.93	
		Height (mm/inch)	75.5 / 2.97	
		Depth (mm/inch)	310 / 12.2	
		Weight (g & lb. oz)	2600 / 5 lb. 11.7 oz	