

MONITOR SUPREME II

1



Magnat



MS 2002



MS 1002



MS 802



MS 202



MS 102



MS SUB 202A



MS SUB 302A



MS CENTER 252

Magnat



MS 2002



MS 1002



MS 802



MS 202



MS 102



MS SUB 202A



MS SUB 302A



MS CENTER 252

Magnat

MONITOR SUPREME II

4



HIGHLIGHTS

- Solid low-resonance MDF cabinet with rounded edges on the front and rear side
- High-quality wood decor, black baffle
- Removable cloth grille
- Tweeter with 1" silk dome, powerful ferrite drive, and new front plate for a balanced reproduction and constant radiation (2002,1002,802,202)
- Tweeter with 1" ultra-light mylar dome and new front plate for precise reproduction (102,252)
- Woofer-midrange with low-distortion, coated cellulose cone and inverse dome
- Very deep precise bass reproduction per reflex double bass construction (2002,1002,802,202)
- Airflex port with rounded reflex opening to avoid wind noise (2002,1002,802,202)
- 12 dB crossover (tweeter 18 dB (2002,1002,802,202) with phase correction
- Gold-plated screw terminal
- Metal (2002,1002,802) - and rubber spikes included
- CE, RoHS and REACH compliant
- Wall-mount option (102)
- Magnetically shielded (252)

Magnet



FEATURES & HIGHLIGHTS

- Level and crossover-frequency adjustable
- High-level input
- Low-level input
- Automatic standby circuit
- Power switch
- Switchable mains voltage
- Solid low-resonance MDF cabinet with rounded edges on the front and rear side
- High-quality wood decor, black baffle
- Removable cloth front cover
- Front-fire construction
- High-power long-throw woofer with Klippel®-optimised magnet system
- Airflex port with rounded reflex opening to avoid wind noise
- Standby circuit with low power consumption <math><0.5\text{ W}</math>
- Anti-resonant rubber feet
- CE, RoHs and Reach compliant

Monitor Supreme 2002

Ash black decor
Mocca decor

ART. NR.: 144 8200 /EAN: 40 18843 48200 2
ART. NR.: 144 8203 /EAN: 40 18843 48203 3

Principle	3 way bass reflex
Equipment	2 x 8" woofer 1 x 6.5" midrange 1" dome-tweeter
Power Handling (RMS/Max)	225 / 450 Watts
Impedance	4 - 8 Ohms
Frequency Response	18 - 40.000 Hz
Crossover Frequencies	350 Hz, 3.500 Hz
Recommended Amplifier Output	30 - 450 Watts
Sensitivity (2.8V/1m)	93 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	267 x 1080 x 335 mm
Weight	23 kg



Monitor Supreme 1002

Ash black decor
Mocca decor

ART. NR.: 144 8100 /EAN: 40 18843 48100 5
ART. NR.: 144 8103 /EAN: 40 18843 48103 6

Principle	3 way bass reflex
Equipment	2 x 6.5" woofer 1 x 6.5" midrange 1" dome-tweeter
Power Handling (RMS/Max)	190 / 380 Watts
Impedance	4 - 8 Ohms
Frequency Response	19 - 40.000 Hz
Crossover Frequencies	500 Hz, 3.300 Hz
Recommended Amplifier Output	30 - 380 Watts
Sensitivity (2.8V/1m)	92 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	215 x 990 x 313 mm
Weight	17 kg



Magnat

Monitor Supreme 802

Ash black decor
Mocca decor

ART. NR.: 144 8080 /EAN: 40 18843 48082 4
ART. NR.: 144 8083 /EAN: 40 18843 48083 1

Principle	2 ½ way bass reflex
Equipment	2 x 6.5" woofer-midrange 1" dome-tweeter
Power Handling (RMS/Max)	170 / 340 Watts
Impedance	4 - 8 Ohms
Frequency Response	22 - 40.000 Hz
Crossover Frequencies	500 Hz, 3.300 Hz
Recommended Amplifier Output	30 - 340 Watts
Sensitivity (2.8V/1m)	92 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	215 x 850 x 273 mm
Weight	14 kg



Monitor Supreme 202

Ash black decor
Mocca decor

ART. NR.: 144 8020 /EAN: 40 18843 48022 0
ART. NR.: 144 8023 /EAN: 40 18843 48023 7

Principle	2 way bass reflex
Equipment	1 x 6.5" woofer-midrange 1" dome-tweeter
Power Handling (RMS/Max)	100 / 200 Watts
Impedance	4 - 8 Ohms
Frequency Response	34 - 40.000 Hz
Crossover Frequencies	3.300 Hz
Recommended Amplifier Output	30 - 200 Watts
Sensitivity (2.8V/1m)	93 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	215 x 354 x 273 mm
Weight	6,2 kg



Magnat

Monitor Supreme 102

Ash black decor
Mocca decor

ART. NR.: 144 8010 /EAN: 40 18843 48010 7
ART. NR.: 144 8013 /EAN: 40 18843 48013 8

Principle	2 way
Equipment	1 x 110 mm woofer-midrange 13 mm dome-tweeter
Power Handling (RMS/Max)	60 / 120 Watts
Impedance	4 - 8 Ohms
Frequency Response	42 - 36.000 Hz
Crossover Frequencies	3.400 Hz
Recommended Amplifier Output	20 - 110 Watts
Sensitivity (2.8V/1m)	89 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	149 x 250 x 190 mm
Weight	2,8 kg



Monitor Supreme Center 252

Ash black decor
Mocca decor

ART. NR.: 144 8250 /EAN: 40 18843 48250 7
ART. NR.: 144 8253 /EAN: 40 18843 48253 8

Principle	2 way
Equipment	1 x 110 mm woofer-midrange 13 mm dome-tweeter
Power Handling (RMS/Max)	75 / 150 Watts
Impedance	4 - 8 Ohms
Frequency Response	40 - 34.000 Hz
Crossover Frequencies	3.400 Hz
Recommended Amplifier Output	20 - 150 Watts
Sensitivity (2.8V/1m)	90 dB
Cabinet surface	Ash black decor , Mocca decor
Dimensions	420 x 145 x 190 mm
Weight	4,9 kg



Magnat

Monitor Supreme Sub 302A

Ash black decor
Mocca decor

ART. NR.: 144 8270 /EAN: 40 18843 48270 5
ART. NR.: 144 8272 /EAN: 40 18843 48272 9

Principle	Powered bass reflex subwoofer, Frontfire
Equipment	300 mm woofer
Power Output (RMS/Max)	100 / 220 Watts
Frequency Response	16 - 200 Hz
Crossover Frequencies	50 - 150 Hz adjustable
Cabinet surface	Ash black decor , Mocca decor
Dimensions (BxHxT)	355 x 440 x 395 mm
Weight	16 kg



Monitor Supreme Sub 202A

Ash black decor
Mocca decor

ART. NR.: 144 8260 /EAN: 40 18843 48260 6
ART. NR.: 144 8262 /EAN: 40 18843 48262 0

Principle	Powered bass reflex subwoofer, Frontfire
Equipment	200 mm woofer
Power Output (RMS/Max)	80 / 160 Watts
Frequency Response	20 - 200 Hz
Crossover Frequencies	50 - 150 Hz adjustable
Cabinet surface	Ash black decor , Mocca decor
Dimensions (BxHxT)	265 x 365 x 345 mm
Weight	9.5 kg



Magnat