



FILE NO.	Bestell No.	UNO ITEM NO.	LENGTH
29212c38	1404171	744121. 5	500+100/-0
29212c38a	1404172	744121. 11	1000+100/-0
29212c38b	1404173	744121. 81	1800+100/-0
29212c38c	1404174	744121. 05	5000+100/-0
29212c38d	1404174	744121. 00	10000+100/-0
29212c38e	1404175	744121. 20	20000+100/-0

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
⑧	FERRITE CORE	ID:9.5*OD:17.5*28.5MM , OUTER MOLD PVC BLACK	2	
⑦	NUT	HEX. NUT #4-40 ,Nickel plating	2	
⑥	VGA CONNECTOR	VGA 15P/F Solder Type, blue PBT insulation, The Pin Gold Plating, The shell Nickel Plating	1	
⑤	MOLDED THUMB SCREW	Nickel Flash #4-40 MOLDER BLACK	2	
④	INNER MOLD	LD-PE	2	
③	OUTER MOLD	PVC COLOR BLACK	2	
②	CABLE	(28AWG BC+S+PVC)*3+28AWG BC*7C+AEB PVC/BLACK OD:7.0±0.2mm	1	
①	VGA CONNECTOR	VGA 15P/M Solder Type, blue PBT insulation, The Pin Gold Plating, The shell Nickel Plating	1	

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10Mohm;
 - Contact resistance:3ohm Max;
 - Dielectric strength:100V AC/Minute, 1mA.
- Computer practical application Test Pass 800*600
- Operation temperature:-10°C ~+60°C
Storage temperature:-20°C ~ +75°C
Operation humidity:10%~85%
Storage humidity:10%~85%
weight of unit (w/o packing): 29212c38/162.7g
- PRINTING:AWM 2919 80°C 30V VW-1 VGA CABLE
- PACKING:1PCS/Renkforce giftbox
- ROSH2.0 AND REACH COMPLIANT

					CUSTOMER		ITEM NO.		SEE THE CHART	
					PRODUCT NAME		VGA M/F CABLE		UNO ITEM NO.	
					DRAWNBY		CHECKBY		APPOBY	
					DATE		REV.		DATE	
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	FERGUS					2015-11-30