

# Radiator Thermostat

Product ref.: 140280



## Product features

- Replaces conventional thermostats and controls the radiator according to the individual needs of the user.
- Up to three adjustable week profiles: The room temperature can be adjusted according to individually tailored heating phases (up to 6 per day with configurable temperature)
- In combination with the Homematic IP Window / Door Contact the temperature is automatically reduced as soon as windows are opened
- Secure installation: Thanks to the metal nut, the device can be securely fixed to all standard radiators
- Easy installation: no need to drain water or to intervene into the heating system
- Manual operation: Temperature changes and activating the boost function (heating up the radiator quickly) can be performed directly on the device

## Technical specifications

Supply voltage	2x 1.5 V LR6/mignon/AA
Current consumption	120 mA (max.)
Battery life	2 years (typ.)
Degree of protection	IP20
Ambient temperature	0 to 50 °C
Dimensions (W x H x D)	58 x 71 x 97 mm
Weight	205 g (incl. battery)
Radio frequency	868.3 MHz/869.525 MHz
Typ. open area RF range	300 m
Connection	M30 x 1.5 mm

## Logistical data

Product reference	140280
EAN code	4047976402809
Short description	HMIP-eTRV
Packing unit	45
Packing dimensions	122 x 112 x 97 mm

## Package contents

Homematic IP Radiator Thermostat
Adapters Danfoss (RA, RAV and RAVL)
Danfoss RAV spigot extension
Support ring
Cylinder head screw M4 x 12 mm and nut M4
1.5 V LR6/mignon/AA batteries (2x)
Operating manual