

Pluggable Switch

Product ref.: 141836



Product features

- Enables switching of connected devices (e.g. electric heaters)
- In connection with the Homematic IP Wall Thermostat the temperature of rooms with electric heaters can be precisely regulated
- Easy installation: quickly and without any tools
- Manual operation: Connected devices can be switched on and off also directly on the device
- Low standby power consumption
- Thanks to the compact design, the pluggable switch does not block the surrounding sockets

Technical specifications

Supply voltage	230 V/50 Hz
Current consumption	16 A (max.)
Standby power consumption	< 0.3 W
Max. switching capacity	3680 W
Load type	ohmic load
Degree of protection	IP20
Ambient temperature	-10 to +35 °C
Dimensions (W x H x D)	70 x 70 x 39 mm (not incl. mains plug)
Weight	154 g
Radio frequency	868.3 MHz/869.525 MHz
Typ. open area RF range	400 m

Logistical data

Product reference	141836
EAN code	4047976418367
Short description	HMIP-PS
Packing unit	45
Packing dimensions	122 x 112 x 97 mm

Package contents

Homematic IP Pluggable Switch

Operating manual