

DATASHEET

6.35mm Plug, stereo, gold plated

Version 01/16

Item no. 1408836



Color.....	Grey
No. of pins.....	3
Audio Channel.....	Stereo
Contact plated.....	Gold
Connection.....	Soldering
Category.....	6.35 mm, gold plated
Connector type.....	Plug, straight
Mating cycles.....	> 3000
Dimension.....	Ø 14.4 x 76.2 (H) mm
Tolerance.....	±1 mm
Contact resistance.....	≤ 10 mΩ
Withstand voltage.....	0.5kV dc
Material and plated.....	zinc alloy/ gold plating
Cable diameter can be used.....	3.5-8.0 mm
Operation temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%
Storage temperature and humidity.....	-25 degree Celsius to +80 degree Celsius / 10%-90%