

## Wireless Switch Actuator 1-channel, plug adapter type F



Product ref.: 132989A0  
**PRODUCT FEATURES**



- Wireless switch actuator enables switching of connected loads via radio commands
- Can be easily mounted without tools - after the device has been plugged in, it is immediately ready for use
- Easy operation - directly on the device or via the WebUI of the Central Control Unit CCU2
- Multiple remote controls can be taught-in
- Low current consumption
- Current switching status of device is indicated by device LED
- Switch on and off delay as well as switch on and switch off duration can be individually adjusted
- Rugged design:  $\cos\phi=1$ : 40,000 switching cycles

### TECHNICAL SPECIFICATIONS

Supply voltage:	230 V/50 Hz
Current consumption:	16 A (max.)
Power consumption in standby:	< 0.6 W
Degree of protection:	IP20
Ambient temperature:	-10 to +35 °C
Radio frequency:	868.3 MHz
Typ. open area RF range:	300 m
Max. switching capacity:	3680 W
Load type:	ohmic load
Relay:	NO contact, 1-pole, $\mu$ contact
Dimensions (W x H x D):	59 x 122 x 40 mm (not incl. mains plug)
Weight:	174 g

### LOGISTIC DATA

Product reference:	132989A0
EAN code:	4047976329892
Short description:	HM-LC-Sw1-PI-DN-R1
Packing unit:	32
Packaging dimensions:	184 x 140 x 73 mm
Total weight:	350.0 g

### PACKAGE CONTENTS

1x Wireless Switch Actuator type F
1x Operating manual in DE, EN, NL and FR