

NANO

Reference: NANO

NANO-R (red)

NANO-N (negro)

Applications:

- Same diameter and performance as the Micro, but even more compact with its height reduced by 35mm and its weight by 40g.
- A true pocket generator.



Technical specifications:

Weight:	250gr
Dimensions:	Height: 50mm. ø: 65mm.
Maximum power:	10 W
Maximum voltage:	5 V
Power delivery at standard operating range:	5 W
Autonomy:	50.000 h. of continuous use
Operation temperature:	150 °C - 400 °C
Average consumption:	50gr. of gas or kerosene/h

Kit contents:

- Nano.
- USB LED bulb.
- Multi-connector.
- Neoprene rubber bag.
- Operating instructions.

Available colours:

