

# THERMIX PRO

- Reference: KIT-THER-PRO
- KIT-THER-PRO-NN

## Applications:

- Shares all the same characteristics as the Thermix BASIC
- Has the additional capability to operate on a wood stove, allowing up to 6 LED bulbs to be powered by the heat generated on the stove surface.
- “Free Energy” for an isolated house in the mountains or snow.
- It comes as a kit in its stylish aluminium case for easy transport and storage.



## Technical specifications:

Weight:	1.350gr
Dimensions:	Length: 316mm. Height: 97mm. Width 137mm.
Maximum power:	18 W
Maximum voltage:	18 V
Power delivery at standard operating range:	9 W
Average power (on stove):	6 W
Average voltage (on stove):	12 V
Autonomy:	50.000 h. of continuous use
Operation temperature:	150 °C - 400 °C
Average consumption:	50gr. of gas or kerosene/h

## Kit contents:

- Thermix Pro.
- Aluminium storage case.
- 12V / USB Converter.
- 2 PowerSpot “Water” 9W-5V bulbs.
- 12V double connector.
- 2 connector-extenders for E27 bulbs.
- Operating instructions.

## Available colours:

