

## Automotive Foam Tape

Version 2/16

Item no. :

1417386 – Red double side tape, black foam, thickness 0.8mm, 20mm (wide) x 30 M (length)

1417387 – Blue double side tape, black foam, thickness 1.0mm, 20mm (wide) x 30 M (length)

### Performance Index

Item: AUTOMOBILE FOAM TAPE

Item	Units	Performance	Test Mode
180°剥离强度 180°Peel Strength	N/25mm	≥20	GB/T 2792—1998
180°解卷强度 180°To Backing	N/25mm	/	GB/T 4850—2002
持粘性 Holding	h/23℃·kg:25mm×25mm	≥48	GB/T 4851—1998
初粘性 Tack	#	15	GB/T 4852—2002
基材 Substrate	/	IXPE	
隔离纸 Seclusion Paper	g/m <sup>2</sup>	60±5, red liner paper	
胶带厚度 Adhesion Thickness	mm	0.8	GB/T 7125—1999
胶水类型 Adhesives	/	acrylic	/
颜色 Color	/	Red/Black	/
拉伸强度 Tensile Strength	N/10mm	≥7.5	GB/T 7753—1987
断裂伸长率 Breakpoint Elongation	%	≥230	GB/T 7753—1987
耐温性 Heat Resistance	℃	-10~100	/
储存期 Storage Life	Year	1	GB/T 7123.2—2002
耐溶剂性 Solvent Resistance	Min	/	GB/T 13353—1992
耐燃性 Resistance Flammability	/	/	GB/T 15903—1995
耐候性 Weathers	/	good	/
备注 Remark			

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.

Distributed Conrad Electronic SE