



TOOLCRAFT

GB Data sheet

Masking tape

Item no. 1417388

a) Technical data

Length..... 50 m
Width 12.5 mm
Colour..... off-white

b) Performance index

Item	Units	Performance	Test mode
180° peel strength	N/25 mm	≥7.5	GB/T 2792-1998
Initial tack	#	≥8	GB/T 4852-2002
Substrate	/	Crepe paper	/
Seclusion paper	g/m ²	/	/
Total thickness	mm	0.14 – 0.16	GB/T 7125-1999
Adhesives	/	Rubber	/
Colour	/	Off-white	/
Tensile strength	N/25 mm	≥60	GB/T 7753-1987
Breakpoint elongation	%	12	GB/T 7753-1987
Heat resistance	°C	80	/
Resistance flammability	/	/	GB/T 15903-1995
Weathers	/	/	/

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

Copyright 2016 by Conrad Electronic SE.

*1417388_V1_0616_02_IPL_ds