

## Masking Tape

Version 02/16

Item no. :

1417388 – 12.5mm(wide) x 50 M (length), off white color

1417389 – 25 mm (wide) x 50 M (length), off white color

1417390 – 38 mm (wide) x 50 M (length), off white color

1417391 – 50 mm (wide) x 50 M (length), off white color

### Performance Index

Item: Masking Tape

Item	Units	Performance	Test Mode
180°Peel Strength	N/25mm	≥7.5	GB/T 2792—1998
Initial Tack	#	≥8	GB/T 4852—2002
Substrate	/	Crepe Paper	/
Seclusion Paper	g/m <sup>2</sup>	/	/
Total Thickness	mm	0.14-0.16	GB/T 7125—1999
Adhesives	/	Rubber	/
Color	/	Off-white	/
Tensile Strength	N/25mm	≥60	GB/T 7753—1987
Breakpoint Elongation	%	12	GB/T 7753—1987
Heat Resistance	°C	80	/
Resistance Flammability	/	/	GB/T 15903—1995
Weathers	/	/	/
Remark			

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.

Distributed Conrad Electronic SE