

Wireless Switch Actuator 1-channel, DIN rail mount

Product ref.: 141378A0
PRODUCT FEATURES



- Connected loads can be switched on and off via the switch actuator
- 230 V switching input can replace existing trigger impulse switches
- Loads of up to 6 A/230 V can be connected
- Standard DIN rail housing with width of 1 WM
- For the independent switching of components without an RS485 connection or an external antenna
- Can be configured and controlled wirelessly via the Homematic Central Control Unit
- Device is equipped with operation/configuration button and display
- Low energy consumption

TECHNICAL SPECIFICATIONS

Supply voltage:	230 V/50 Hz
Current consumption:	6 A (max.)
Power consumption in standby:	0.35 W
Max. switching capacity:	1380 W
Degree of protection:	IP20
Ambient temperature:	5 to 35 °C
Load type:	ohmic load
Installation:	mounting rail (DIN rail) according to EN50022
Dimensions (W x H x D):	18 x 65 x 87 mm
Weight:	63 g
Radio frequency:	868.3 MHz
Typ. open area RF range:	200 m

LOGISTIC DATA

Product reference:	141378A0
EAN code:	4047976413782
Short description:	HM-LC-Sw1-DR
Packing unit:	144
Packaging dimensions:	122 x 93 x 36 mm
Total weight:	121.9 g

PACKAGE CONTENTS

1x Wireless Switch Actuator
1x Operating manual in DE and EN