



Einhell

ACCESSORY



Battery

18V 2,0 Ah Power-X-Change

Item No.: 4511395

Ident No.: 11039

Bar Code: 4006825610369

The Einhell 18V 2.0 Ah PXC is a rechargeable battery which is designed for universal use in the entire PXC product family. A single rechargeable battery and a single charger for all tools saves significant costs of buying, and universal use also helps protect the environment and provides flexibility at the same time. The ABS process-controlled active battery management system ensures max. safety, optimum tool performance, max. operating time + max. service life. The high-quality rechargeable battery resists the memory effect and self-discharge. The housing is rubberized for high impact protection and grip.

Features & Benefits

- Universal usability for all Power X-Change rechargeable devices:
- Saving money, protecting the environment, and flexibility
- The ABS process-controlled battery management system stands for
- max. safety, optimum performance, operating time + lifetime
- Freedom of cordless operation: No tangled cables and free working
- High-quality Li-Ion cells means no memory effect,
- low self-discharge and high, constant power
- Current charge level indicated by 3-stage LED display
- Impact protection and good grip thanks to rubber-coated housing
- Trough handle for easy removal
- Housing protected against dust, corrosion and mechanical damage
- Suitable for TWIN-PACK use in power demanding 36V applications



Technical Data

- | | |
|-----------------------|----------|
| - Voltage | 18 V |
| - Battery capacity | 2 Ah |
| - Max. power | 450 W |
| - Amount of batteries | 1 Pieces |



Logistic Data

- | | |
|--------------------------------------|--------------------|
| - Product weight (kg) | 0.41 |
| - Gross weight (kg) | 0.44 |
| - Dimensions single packaging | 82 x 57 x 161 mm |
| - Pieces per export carton | 24 Pieces |
| - Gross weight export carton | 10.9 kg |
| - Dimensions export carton | 350 x 280 x 215 mm |
| - Container quantity (20"/40"/40"HC) | 28800 0 0 |

