



NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10MΩ;
 - Contact resistance:3Ω Max;
 - Dielectric strength:150V AC/Minute, 1mA.
- Operation temperature:-10℃ ~+60℃
Storage temperature:-20℃ ~ +75℃
Operation humidity:10%~85%
Storage humidity:10%~85%
- PRINT WORD: AWM 20276 80℃ 30V VW-1 USB 3.0 SUPER SPEED CABLE
- ROHS2.0 and REACH compliant
- PACKING:1PCS/Renkforce giftbox

MATERIAL LIST:

⑤	OUTER MOLD	PVC COLOR FOR Blue	2	
④	INNER MOLD	LD-PE	2	
③	USB B TYPE	USB3.0 MICRO B/M 10PIN SOLDER TYPE, BLACK PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
②	USB A TYPE	USB3.0 A/M 9PIN SOLDER TYPE, BLUE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
①	CABLE	(28AWG BC*1P+28AWG BC+WAM)*2+28AWG BC*2C+24AWG BC*2C+AEB, PVC jaket/Blue(285C) OD:5.5±0.2mm	1	

FILE NO.	B/N	LENGTH	COLOUR	Packing
29212c90	1421511	300+100/-0MM	Blue	VP1:10.5x14cm (depth:2cm)
29212c90a	1421512	500+100/-0MM	Blue	VP1:10.5x14cm (depth:2cm)
29212c90b	1421514	1000+100/-0MM	Blue	VP1:10.5x14cm (depth:2cm)
29212c90c	1421515	1800+100/-0MM	Blue	VP1:10.5x14cm (depth:3cm)
29212c90d	1421516	3000+100/-0MM	Blue	VP1:10.5x14cm (depth:3cm)

NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
	Alvan	REVISION MOULDING AND PRINT WORD	2017-07-24	A2
	Alei	Alvan CHANGE PRINT WORD	2018.01.04	A1
		NEW	2016.04.11	A
	BY	CHK	REVISION RECORD MODIFICATIONS	DATE
				REV.

CUSTOMER	ITEM NO.	SEE THE CHART
PRODUCT NAME	USB 3.0 AM-MICRO BM CABLE	UNO ITEM NO.
DRAWNBY	CHECKBY	APPOBY
Alei	Alvan	2018.07.24