

© COPYRIGHT


REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
T1	REVISED PER ECO-11-005294	05APR11	HMR

.008 MAX CUT-OFF
TAB FOR -6 ONLY

.695

.015 MAX
CUT-OFF TAB



.078/.081 DIA.


VIEW A-A

.055
.125

.150
.125

.105-.130

SECT. B-B



.020 MIN

.170
.165


.150-.175

SECT C-C

⚠ NICKEL ON ENTIRE TERMINAL WITH .000030
GOLD OVER INSIDE OF MATING AREA AND
WIRE BARREL.

GOLD	⚠	.012 PH. BRZ.	60619-7
GOLD	⚠	.012 BRASS	-5
TIN		.012 PH. BRZ	-4
TIN		.012 BRASS	60619-1
FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .015 ANGLES ±	CONTRACT NO
	DR M. FEHER 11-14-79
MATERIAL SEE TABLE	CHK D.S. Heide 1/4/80
	APPO in Solonville 1-7-80
FINISH SEE TABLE	WIRE RANGE 20-14 AWG
	INSULATION DIA .130 MAX

 TE Connectivity		
NAME SOCKET, LOOSE PIECE, COMMERCIAL MATE-N-LOK		
SIZE A	CODE IDENT. NO 00779	DRAWING NO 60619
SCALE	SHEET	

CUSTOMER DRAWING