



Designation: 16630 101 001

Battery Requirement: 3 x AAA

Bulb required: 4pcs 5mm cool White LED

Luminous intensity: High: 50 lumens or 106 cd
Low: 28 lumens or 54 cd

Range: 20 m (calculated distance at maximum luminous intensity with an illuminance of 0.25lux).

Weight: 44 g (without batteries).

Material: ABS (Acrylonitrile Butadiene Styrene)
PC (Polycarbonate)
Rubber
All contact parts made of bronze or nickel plated steel.

Dimensions (mm):

A	46.7
B	62
C	41
D	35

Run Time: High mode: 16 hours (with VARTA HE alkaline battery)
Low mode: 34 hours (with VARTA HE alkaline battery)

Features:

- Push Switch (High 4 LED On/ Low 2 LED On / Off)
- 4pcs 5mm super bright cool white LED
- PC material body with over-mould rubber head for maximum durability
- Compact and lightweight design
- Shatterproof lens
- 20° downward beam design
- 2 meters drop test
- 10,000 switch cycle life