



# **ALLNET**

## **ALL-MC107-ST-MM**

### **Media Converter 10/100BaseTX auf 100BaseFX/ST**

- *1x 10/100BaseTX Ethernet TP Port, 1x100BaseFX Ethernet Fiber Port*
- *TP Port supports Half/Full-Duplex, Auto-MDI/MDI-X und Auto-Negotiation*
- *FX Fiber Port supports Multi Mode ST*
- *Ethernet 802.3x Flow Control*

*Art.-Nr.105640*

Note: Product specification is subject to change without notice.



Item	Specification
Standards:	IEEE 802.3 10BaseT IEEE 802.3u 100BaseTX/100BaseFX IEEE 802.3x FLOW Control
Features:	1x 10/100BaseT with RJ-45 Connector 1x 100BaseFX with Fiber Connector MM,SC
Data Transfer Rate:	Ethernet: 10Mbps/Half-Duplex ; 20Mbps/Full-Duplex Fast Ethernet: 100Mbps/Half-Duplex; 200Mbps/Full-Duplex
Transmission Media:	10BaseT Cat. 3, 4, 5 UTP/STP, bis zu 100 m 100BaseTX Cat. 5 UTP/STP, bis zu 100 m 100BaseFX 50/125µm oder 62.5/125µm Multi Mode ST-Typ LWL, bis zu 1km
Led Indicators:	Power on Per Port:(TX): Link/Act, Speed, FDX/COL ; (FX): Link/Act, FDX/COL
Power Requirement:	DC 5V/2A external Power Supply
Power Consumption:	2,5 Watts (Max)
Dimensions:	94 × 71 × 26 mm (L x W x H)
Weight:	230g (only MC)
Environment:	Temperature operating: 0 ~ 50 °C Humidity operating: 10% ~ 90% (non-condensing) Temperature storage: -20 ~ 70 °C Humidity storage: 10% ~ 90% (non-condensing)
Certifications:	CE