

## Midi Security Kit PRO FullHD 1080P TX-51

Surveillance set with receiver and two cameras for indoor and outdoor use



### Features RECEIVER "MIDI":

- Real-time monitor
- Storage function
- Backup function
- Record playback function
- Network operation
- Alarm activation function
- PTZ control

### Technical Specifications RECEIVER "MIDI":

- Supports HDCVI/IP cameras video input
- H.264 dual-stream video compression
- All channel 1080P realtime recording
- Support VGA/HDMI video output at the same time
- 4-channel synchronous real-time playback, GRID interface, smart search
- Supports multi-brand network cameras from other manufacturers
- ONVIF version 2.3 conformance
- 1 built-in SATA port supporting HDD up to 4TB
- 2 built-in ports USB2.0 and higher
- Multiple network monitoring: WEB viewer, CMS (DSS/SMART PSS), Smartphone (Technaxx My Secure Pro)
- Weight / Dimensions: 1.25 kg (without HDD) / (L) 27.0 x (W) 20.5 x (H) 4.1 cm

### Features BULLET CAMERA:

- High-performance CMOS image sensor with 2.4 Mega pixel
- Supports HDCVI HD video output
- Transmission distance up to 300m via 75-3 coaxial cable without data loss
- High speed, long distance real-time transmission
- Automatic ICR switch to realize surveillance both in the daytime and at night
- Automatically: exposure, white balance, electronic shutter, gain function
- Restore clear and vivid video
- Supports IR function with IR LED distance max. 15m
- Protection class IP66 (dust & waterproof)

### Technical Specifications BULLET CAMERA:

- Video resolution: 1980 × 1225 @ 30 fps (PAL)
- Video frame rate: 25/30/50/60 fps @ 720P & 25/30 fps @ 1080p
- Min. illumination: 0.05 Lux @ F1.2 (AGC ON), 0 Lux with IR switched on
- Electronic shutter: 1/3 sec. ~ 1/100000 sec. (PAL)
- 1-channel BNC HDCVI high definition video output & CVBS standard definition video output
- BLC (Back Light Control): automatically
- Noise reduction of 2D/3D
- Colour or Black/White: selectable
- IR light only is active for video recordings in night mode
- Horizontal angle of view: 105.5° ~ 32.9°
- Focal length: 2.7 ~ 12.0mm / automatic zoom
- Fixed aperture for the brightness
- Working temperature: - 30°C ~ 60°C
- Power: DC 12V ± 10%
- Power consumption: 7.44W max. (Input 12V/0.62A) IR 15m max.
- Indoor and outdoor installation: wall mount
- Weight / Dimensions: 550 g / (L) 21,3 x (W) 8,0 x (H) 7,2 cm

### Features DOME CAMERA:

- High-performance CMOS image sensor with 2.4 Mega pixel
- Supports HDCVI HD video output
- Transmission distance up to 300m via 75-3 coaxial cable without data loss
- High speed, long distance real-time transmission
- Automatic ICR switch to realize surveillance both in the daytime and at night
- Automatically: exposure, white balance, electronic shutter, gain function
- Restore clear and vivid video
- Supports IR function with IR LED distance max. 15m
- Protection class IP66 (dust & waterproof) & IK10 (shockproof)

### Technical Specifications DOME CAMERA:

- Video resolution: 1980 × 1225 @ 30 fps (PAL)
- Video frame rate: 25/30/50/60 fps @ 720P & 25/30 fps @ 1080p
- Min. illumination: 0.05 Lux @ F1.2 (AGC ON), 0 Lux with IR switched on
- Electronic shutter: 1/3 sec. ~ 1/100000 sec. (PAL)
- 1-channel BNC HDCVI high definition video output & CVBS standard definition video output
- BLC (Back Light Control): automatically
- Noise reduction 2D/3D
- Colour or Black/White: selectable
- IR light only is active for video recordings in night mode
- Horizontal angle of view: 105.5° ~ 32.9°
- Focal length: 2.7 ~ 12.0mm / automatic zoom
- Fixed aperture for the brightness
- Power: DC 12V ± 10%
- Power consumption: 8.6W max. (Input 12V/0.72A) IR 15m max.
- Indoor and outdoor installation: wall mount / ceiling mount
- Working temperature: - 30°C ~ 60°C
- Weight / Dimensions: 450 g / Ø 12.2 x (H) 8.9 cm



### Package Contents:

#### Receiver for Midi Security Kit PRO FullHD 1080P TX-51:

3x Power Adapter, 2x BNC 18.3m video cable, Optical Mouse, SATA cable, CD, User Manual Receiver

#### Bullet Camera for Midi Security Kit PRO FullHD 1080P TX-51:

3x screws and 3x dowels, User Manual Bullet Camera

#### Dome Camera for Midi Security Kit PRO FullHD 1080P TX-51:

3x screws and 3x dowels, User Manual Dome Camera

### EAN-Code:

4260358121321

Article-No. 4564