

Additional Bullet camera for Security Kit PRO FullHD 1080P TX-50 and TX-51

Surveillance camera for indoor and outdoor use









- Video resolution: 1980 × 1225 @ 30 fps (PAL)
- High-performance CMOS image sensor with 2.4 Mega pixel
- Supports HDCVI HD video output
- Transmission distance up to 300m via 75-3 coaxial cable without data loss
- High speed, long distance real-time transmission
- Automatic ICR switch to realize surveillance both in the daytime and at night
- Automatically: exposure, white balance, electronic shutter, gain function
- Restore clear and vivid video
- Supports IR function with IR LED distance max. 15m
- Protection class IP66 (dust & waterproof)



Technical Specifications:

- Video frame rate: 25/30/50/60 fps @ 720P & 25/30 fps @ 1080p
- Min. illumination: 0.05 Lux @ F1.2 (AGC ON), 0 Lux with IR switched on
- Electronic shutter: 1/3 sec. \sim 1/100000 sec. (PAL)
- \bullet 1-channel BNC HDCVI high definition video output & CVBS standard definition video output
- BLC (Back Light Control): automatically
- Noise reduction of 2D/3D
- Colour or Black/White: selectable
- IR light only is active for video recordings in night mode
- Horizontal angle of view: 105.5° ~ 32.9°
- Focal length: 2.7 ~ 12.0mm / automatic zoom
- Fixed aperture for the brightness
- Working temperature: 30°C ~ 60°C
- Power: DC 12V ± 10%
- Power consumption: 7.44W max. (Input 12V/0.62A) IR 15m max.
- Indoor and outdoor installation: wall mount
- Weight / Dimensions: 550 g / (L) 21,3 x (W) 8,0 \times (H) 7,2 cm

Package Contents:

- Bullet camera for Security Kit PRO FullHD 1080PTX-50 and TX-51
- 1x BNC 18.3m video cable
- 3x screws and 3x dowels
- User Manual

EAN-Code:

4260358121338 Article-No. 4566